

# MONO

A025PJI050L51-10 CHROME

EAN 4031582364606



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Load capacity Static	132.28 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.83 in
Overall weight	1.72 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.71 in
Hardness of tread (A)	85 Shore A

## HOUSING

Material	Polypropylene
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	0.98 in
Swivel radius	2.83 in
Swivel interference	5.65 in

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

# MONO

A025PJI050L51-10 CHROME

EAN 4031582364606



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

