PRODUCT INFORMATION

STYLEA

5925UOI075S70-10X15 TFR

EAN 4031582385687



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	88 mm
Overall width	54 mm
Overall weight	0.16 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Swivel radius	87 mm
Swivel interference	174 mm
Thread diameter	10 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

© Copyright 2026 TENTE International GmbH