

STYLEA

5923UJI065B10-11X20/10D27 9011/9011

EAN 4031582335712



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement Noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------|
| Product Name | Stylea |
| Type | Swivel castor with intermittent brake |
| Standard | EN12529 - Swivel Chairs Castors |
| Load capacity at 3 km/h | 50 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 100 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 68 mm |
| Overall width | 43 mm |
| Overall weight | 0.13 kg |

HOUSING

| | |
|---------------------|--------------------------|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Stem, swiveling |
| Housing Color | Graphite black (RAL9011) |
| Offset | 25 mm |
| Swivel radius | 53 mm |
| Swivel interference | 106 mm |
| Dome diameter | 27 mm |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread Color | Anthracite grey (RAL7016) |
| Wheel Color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 8 mm |
| Axle Hole Diameter | 0 mm |
| Hub Length | 0 mm |
| Body width | 8 mm |
| Hardness of tread (A) | 87 Shore A |

FITTING

| | |
|---------------|----------------------------------|
| Fitting type | Stem with grip ring, with collar |
| Stem diameter | 11 mm |
| Stem length | 20 mm |

STYLEA

5923UJI065B10-11X20/10D27 9011/9011

EAN 4031582335712

Order number 00078110

Product Drawings



BETTER MOBILITY. BETTER LIFE.

