PRODUCT INFORMATION

AGILA

2477DIK075R47-27-30

EAN 4031582325928



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	55 kg
Electric Conductive	No
Stainless	No
Load capacity Static	110 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	103 mm
Overall weight	0.43 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	24 mm
Swivel radius	80 mm
Swivel interference	160 mm

WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	27 mm
Expander fitting (Maximum)	30 mm
Hint	Please indicate required tube innerdiameter when ordering.

© Copyright 2026 TENTE International GmbH


AGILA


2477DIK075R47-27-30

EAN 4031582325928

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH