

# COMPACTA

1530PJO050P41

EAN 4031582428407



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	23 kg
Load capacity Static	46 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	60 mm
Overall weight	0.084 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	23 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	22 mm
Swivel radius	47 mm
Swivel interference	94 mm

## FITTING

Fitting type	Square plate
Plate length	37 mm
Plate width	37 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	30 mm