

NOVATECH

ETX085X80-Ø12 HL85-B

EAN 4031582369670



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip kućišta Tocak

Nosivost na 3 km/h 800 kg

Statički Nosivost 1600 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj, zapečaceno
stitnici omotaca	Sa threadguard
Prečnik	85 mm
Širina omotac	80 mm
dimenzija rupa osovina	12 mm
dužina glavcine	85 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip zaptivke	B
Pogodno za	linde

TEHNIČKI CRTEŽI

