

NOVATECH

ETX085X80-Ø12 HL85-B

EAN 4031582369670



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj, zapevaceno
stitnici omotaca	Sa threadguard
Prečnik	85 mm
Širina omotac	80 mm
dimenzija rupa osovina	12 mm
duzina glavčine	85 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip zaptivke	B
Pogodno za	linde

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 800 kg

Statički Nosivost 1600 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

NOVATECH

ETX085X80-Ø12 HL85-B

EAN 4031582369670



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

