

# NOVATECH

ETP 085X115-Ø30 HL115

EAN 4031582330380  
Order number 00839737



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	85 mm
Tread width	115 mm
Axle hole diameter	30 mm
Hub length	115 mm
Body width	115 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6006

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	850 kg
Load capacity at 6 km/h	680 kg
Load capacity Static	1700 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.524 kg

# NOVATECH

ETP 085X115-Ø30 HL115

EAN 4031582330380  
Order number 00839737



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

