

ALPHA STAINLESS

8478UFC160P63

EAN 4031582422504



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ●
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall Height	200 mm
Overall weight	1.85 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Housing Color	Stainless steel

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Hardness of tread (A)	64 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA STAINLESS

8478UFC160P63

EAN 4031582422504



BETTER MOBILITY. BETTER LIFE.

Product Drawings

