

PRODUCT INFORMATION

MAXTECH

PNR400x90-Ø10 HL129 yellow with axle

EAN 4031582438192



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	319.67 lb
Electric conductive	no
Stainless	no
Load capacity Static	639.34 lb
Overall weight	6.61 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in

MAXTECH

PNR400x90-Ø10 HL129 yellow with axle

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.

Product Drawings

