

PURETECH

PIR 125X37-Ø12 HL48

EAN 4031582320350
Broj porudžbine 00030824

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	37 mm
dimenzija rupa osovina	12 mm
dužina glavcine	48 mm
Širina tela	37 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,473 kg

PURETECH

PIR 125X37-Ø12 HL48

EAN 4031582320350
Broj porudžbine 00030824



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

