

PLATE

P10-40x27 / 8

EAN 4031582320152



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

| | |
|-----------------------------|--------------------------|
| Fitting type | Stem with U-shaped plate |
| Plate length | 40 mm |
| Plate width | 27 mm |
| Plate hole length (Maximum) | 32 mm |
| Plate hole width (Maximum) | 32 mm |
| Plate hole diameter | 4 mm |

PERFORMANCE

Corrosion Resistance ●●●○○

CORE ATTRIBUTES

| | |
|-------------------------|-----------|
| Product Name | Plate |
| Type | Accessory |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Overall Height | 8 mm |