

DELTA CENTRAL

3645ITP160P67 OH225 SOFT CV

EAN 4031582366501
Order number 00835383



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta central
Type	Swivel castor with wheel brake
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	550 kg
Load capacity at 6 km/h	440 kg
Load capacity Static	1100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	225 mm
Overall width	94 mm
Overall weight	3.89 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Aluminium
Tread hardness	soft
Tread profile	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic grey A (RAL7042)
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad, reinforced
Swivel bearing	Precision ball bearing
Colour	Blue passivated
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm
Dome diameter	94 mm

FITTING

Fitting type	Plate with central locking
Plate length	142 mm
Plate width	110 mm
Plate hole length (Maximum)	77.5 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	13 mm

DELTA CENTRAL

3645ITP160P67 OH225 SOFT CV

EAN 4031582366501
Order number 00835383



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

