

PURETECH AIR

DQP260X85-Ø20 HL74 6PR

EAN 4031582428858



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Pneumatic tire, block profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	10.24 in
Tread width	3.35 in
Axle hole diameter	0.79 in
Hub length	2.91 in
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Housing type	Wheel
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb
Overall weight	3.45 lb

PURETECH AIR

DQP260X85-Ø20 HL74 6PR

EAN 4031582428858



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

