

DURATECH

TOP 200X50-Ø25 HL60

EAN 4031582322736

Broj porudžbine 00802937



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6205

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	1200 kg
Nosivost na 6 km/h	1000 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,601 kg

DURATECH

TOP 200X50-Ø25 HL60

EAN 4031582322736

Broj porudžbine 00802937



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

