

# PURETECH

PIP150X32-Ø8

EAN 4031582356694  
Order number 00038560



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
	soft
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Axle hole diameter	0.31 in
Hub length	1.44 in
Hardness of tread (A)	75 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.95 lb

# PURETECH

PIP150X32-Ø8

EAN 4031582356694  
Order number 00038560



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

