

FOOTMASTER

FOOT MASTER GASD-100-ASF-HUD

EAN 4031582495218



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	310 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	150 mm
Overall width	128 mm
Overall weight	8.45 kg

HOUSING

Offset	32 mm
Swivel radius	90 mm
Swivel interference	180 mm
Dome diameter	112 mm

WHEEL

Bearing	Unmachined hub
Diameter	100 mm
Tread width	30 mm
Body width	30 mm

FITTING

Plate length	112 mm
Plate width	112 mm
Plate hole length (Maximum)	92 mm
Plate hole width (Maximum)	92 mm
Plate hole diameter	9 mm

FOOTMASTER

FOOT MASTER GASD-100-ASF-HUD

EAN 4031582495218

Order number 00800106
Product Drawings



BETTER MOBILITY. BETTER LIFE.

