

# MAXTECH

PA0050X19,5-Ø6X22,6 + ASBUS

EAN 4031582381221



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.03 kg

## WHEEL

Diameter	50 mm
Tread width	19.5 mm
Axle hole diameter	6 mm
Hub length	22.6 mm