

STYLEA

5925UAI055B10-11X20

EAN 4031582456257



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.48 in
Overall width	1.46 in
Overall weight	1.43 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.17 in
Tread width	0.43 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.52 in
Swivel interference	5.04 in
Dome diameter	0.71 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

STYLEA

5925UAI055B10-11X20

EAN 4031582456257



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

