

STYLEA

5920UOI075L51-11 DM20X43ALU

EAN 4031582335972



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	88.5 mm
Overall width	53 mm
Overall weight	0.124 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	20 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	11 mm

PRODUCT INFORMATION

STYLEA

5920UOI075L51-11 DM20X43ALU

EAN 4031582335972



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

