

# PURETECH

PIR100X35-Ø12 HL44,4

EAN 4031582320336  
Order number 00030826



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.38 in
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.62 lb

PRODUCT INFORMATION

# PURETECH

PIR100X35-Ø12 HL44,4

EAN 4031582320336  
Order number 00030826



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

