

LEVINA

5377PIP100R05-18X62

EAN 4031582363005



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance ●●●○○

Movement noise ●●●●○

Attrition ●●●○○

Corrosion resistance ●●●●○

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Levina |
| Housing type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 137 mm |
| Overall weight | 0.734 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 75 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material fork | Polyamide |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Offset | 36 mm |
| Swivel radius | 98 mm |
| Swivel interference | 196 mm |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 18 mm |
| Bolt length | 62 mm |



Universal Design Award



Deutscher Designer Club

LEVINA



5377PIP100R05-18X62

EAN 4031582363005



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Universal
Design
Award



Deutscher
Designer
Club