

KAPPA LOAD

9650FTP300P63 CL67

EAN 4031582314274
Order number 00830239



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3174.65 lb
Load capacity at 3.7 mph	2645.54 lb
Load capacity Static	5291.09 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	13.98 in
Overall width	4.33 in
Overall weight	32.62 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	11.81 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Color	Blue passivated
Offset	2.76 in
Swivel radius	8.76 in
Swivel interference	17.52 in
Dome diameter	4.37 in

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

KAPPA LOAD

9650FTP300P63 CL67

EAN 4031582314274
Order number 00830239



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

