PRODUCT INFORMATION

DURATECH SILENT

HUR 100x36-Ø12 HL44 tyre-black

EAN 4031582319637



Image may differ from the original product

WHEEL

Body material	Damping, hybrid material
Tread material	Polyamide
Bearing	Roller bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.73 in
Body width	1.42 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●●○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.88 lb

© Copyright 2026 TENTE International GmbH


DURATECH SILENT

HUR 100x36-Ø12 HL44 tyre-black

EAN 4031582319637

Order number 00033610

Product Drawings



© Copyright 2026 TENTE International GmbH