

PRODUCT INFORMATION

# NOVATECH

FTP 400X100-Ø40 HL120

EAN 4031582319491  
Order number 00801334



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 15.75 in               |
| Tread width           | 3.94 in                |
| Axle hole diameter    | 1.57 in                |
| Hub length            | 4.72 in                |
| Body width            | 3.94 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Novatech                     |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph    | 8465.74 lb                   |
| Load capacity at 3.7 mph    | 7054.78 lb                   |
| Load capacity Static        | 14109.57 lb                  |
| Temperature range (Minimum) | 14 °F                        |
| Temperature range (Maximum) | 140 °F                       |
| Overall weight              | 62.25 lb                     |

# NOVATECH

FTP 400X100-Ø40 HL120

EAN 4031582319491  
Order number 00801334



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

