

## NOVATECH

ITP 160x50-Ø20 HL60 soft cv

EAN 4031582329544



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                              |
|----------------------------|------------------------------|
| Tread profile              | konveksan                    |
| Tread hardness             | mekan                        |
| Materijal za telo          | Aluminijum                   |
| materijal omotaca          | Poliuretana, liveno          |
| Nošenje                    | precizini kuglični lezaj     |
| Boja Tocak                 | Saobraćajna siva A (RAL7042) |
| stitnici omotaca           | Bez stražara                 |
| Prečnik                    | 160 mm                       |
| Širina omotac              | 50 mm                        |
| dimenzija rupa osovina     | 20 mm                        |
| dužina glavcine            | 60 mm                        |
| Širina tela                | 50 mm                        |
| Teškoća gazećeg omotac (A) | 80 Šešelj A                  |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ● ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Novatech                     |
| Tip                            | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 550 kg                       |
| Nosivost na 6 km/h             | 440 kg                       |
| Električni provod              | no                           |
| nerdjajuci                     | no                           |
| Statički Nosivost              | 1100 kg                      |
| Temperaturni opseg (Minimalno) | -10 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |
| Ukupna težina                  | 1.2 kg                       |




# NOVATECH

ITP 160x50-Ø23, H160x50H cv

EAN 4031582329544

Broj porudžbine 00833312



BETTER MOBILITY. BETTER LIFE.