

# SOCKET

R40-18x18 / 11

EAN 4031582090178



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

|               |                          |
|---------------|--------------------------|
| Fitting type  | Synthetic socket, square |
| Bolt diameter | 18 mm                    |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Corrosion Resistance | ● ● ● ○ ○ |
|----------------------|-----------|

## CORE ATTRIBUTES

|                         |           |
|-------------------------|-----------|
| Product Name            | Socket    |
| Type                    | Accessory |
| Load capacity at 3 km/h | 40 kg     |
| Electric Conductive     | No        |
| Stainless               | No        |
| Load capacity Static    | 80 kg     |
| Overall Height          | 36 mm     |
| Overall weight          | 0.01 kg   |

# SOCKET

R40-18x18 / 11

EAN 4031582090178

Order number 00009044  
Product Drawings



BETTER MOBILITY. BETTER LIFE.



| Bezeichnung | A  | B    | C  |
|-------------|----|------|----|
| R40-16x16   | 16 | 20   | 36 |
| R40-17x17   | 17 | 19   | 36 |
| R40-18x18   | 18 | 20   | 36 |
| R40-21x21   | 21 | 23,5 | 36 |
| R40-22x22   | 22 | 24,5 | 36 |
| R40-23x23   | 23 | 25,5 | 36 |
| R40-26x26   | 26 | 30   | 36 |