

# SUPRATECH

PJP3X1.25-Ø9.8 HL41

EAN 4031582436129



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	76.2 mm
Tread width	31.75 mm
Axle hole diameter	9.8 mm
Hub length	41 mm
Hardness of tread (A)	77 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg