

# MAXTECH

UAR200X50-Ø20 HL58 RED

EAN 4031582419320



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,035 kg

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj
štitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	58 mm
Teškoća gazećeg omotac (D)	40 Šor D

# MAXTECH

UAR200X50-Ø20 HL58 RED

EAN 4031582419320



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

