

LUMINA

A523Y0I050B10-11X20/10D38 9011/9011

EAN 4031582341249



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster with intermittend brake
Load capacity at 1.8 mph	88.18 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.4 in
Overall width	2.17 in
Overall weight	0.22 lb



BETTER MOBILITY. BETTER LIFE.

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	0.79 in
Swivel radius	2.05 in
Swivel interference	4.09 in
Dome diameter	1.5 in

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.31 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

LUMINA

A523YOI050B10-11X20/10D38 9011/9011

EAN 4031582341249

Order number 00075213

Product Drawings



BETTER MOBILITY. BETTER LIFE.

