

DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315
Order number 00829018



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	1.26 in
Axle hole diameter	0.47 in
Hub length	1.26 in
Body width	1.26 in
Hardness of tread (D)	75 Shore D
Bearing type	6201

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	639.34 lb
Load capacity at 3.7 mph	529.11 lb
Load capacity Static	1058.22 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.37 lb

DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315
Order number 00829018



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

