PRODUCT INFORMATION

MAXTECH

UAP 125x40-Ø20 HL60 natural/3004

EAN 4031582322965



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	40 mm
Hardness of tread (A)	96 Shore A
Hardness of tread (D)	48 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.66 kg

© Copyright 2026 TENTE International GmbH


MAXTECH

UAP 125x40-Ø20 HL60 natural/3004

EAN 4031582322965

Order number 00034205

Product Drawings



© Copyright 2026 TENTE International GmbH