

DURATECH

UOR200X50-Ø25 TFR

EAN 4031582390711



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	58 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	700 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.88 kg

DURATECH

UOR200X50-Ø25 TFR

EAN 4031582390711



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

