

# MAXTECH

UAD200X50-Ø20 HL58 RED

EAN 4031582419337



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.91 kg

# MAXTECH

UAD200X50-Ø20 HL58 RED

EAN 4031582419337



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

