

FOOTMASTER

FOOT MASTER GDR- 80-S-NYN

EAN 4031582413328



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	500 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	102 mm
Ukupna širina	86 mm
Ukupna težina	1.2 kg

KUCISTE

Boja	Beli
ofset	46 mm
okretni radijus	77.5 mm
Otpor okretanju	155 mm
Prečnik kupole	86 mm

TOCAK

Nošenje	kotrljajuci lezaj, navlažen
Boja Tocak	Crna
Prečnik	63 mm
Širina omotac	30 mm
Širina tela	30 mm

FOOTMASTER

FOOT MASTER GDR- 80-S-NYN

EAN 4031582413328

Broj porudžbine 00062083
Product Drawings



BETTER MOBILITY. BETTER LIFE.

