

# PURETECH

PVR200x50-Ø15 HL58

EAN 4031582442267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread Material Mix    | Solid rubber, black |
| Bearing               | Roller bearing      |
| Threadguards          | Without threadguard |
| Diameter              | 200 mm              |
| Tread width           | 50 mm               |
| Axle Hole Diameter    | 15 mm               |
| Hub Length            | 58 mm               |
| Hardness of tread (A) | 85 Shore A          |

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 205 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 410 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 1.26 kg                       |

# PURETECH

PVR200x50-Ø15 HL58

EAN 4031582442267



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

