

# STYLEA

5920UOI065B10-11X20/10D27 9011/9011

EAN 4031582335682  
Order number 00078022



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Stylea                      |
| Housing type                | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 110.23 lb                   |
| Load capacity Static        | 220.46 lb                   |
| Temperature range (Minimum) | -4 °F                       |
| Temperature range (Maximum) | 140 °F                      |
| Overall height              | 2.68 in                     |
| Overall width               | 1.69 in                     |
| Overall weight              | 0.27 lb                     |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread color           | Graphite black (RAL9011)       |
| Wheel color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 2.56 in                        |
| Tread width           | 0.31 in                        |
| Axle hole diameter    | 0 in                           |
| Hub length            | 0 in                           |
| Body width            | 0.31 in                        |
| Hardness of tread (D) | 65 Shore D                     |

## HOUSING

|                     |                          |
|---------------------|--------------------------|
| Material            | Polyamide                |
| Fork shape          | Twin wheel housing       |
| Swivel bearing      | Stem, swiveling          |
| Color               | Graphite black (RAL9011) |
| Offset              | 0.98 in                  |
| Swivel radius       | 2.09 in                  |
| Swivel interference | 4.17 in                  |
| Dome diameter       | 1.06 in                  |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 0.43 in                          |
| Stem length   | 0.79 in                          |

PRODUCT INFORMATION

# STYLEA

5920UOI065B10-11X20/10D27 9011/9011

EAN 4031582335682  
Order number 00078022



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

