

PRODUCT INFORMATION

# DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Plastic thermoset, heat-resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Wheel Color	Black
Diameter	80 mm
Tread width	35 mm
Axle Hole Diameter	8 mm
Hub Length	45.5 mm
Body width	35 mm
Hardness of tread (D)	90 Shore D

## PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.21 kg

# DURATECH HEAT

BOG 080x35 HL45,5 asm.

EAN 4031582317695

Order number 00035369  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

