

STYLEA

5925UJI075S70-10X15 DOM20 TFR

EAN 4031582385731



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 83 mm |
| Overall width | 54 mm |
| Overall weight | 0.19 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 75 mm |
| Tread width | 8 mm |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 62 mm |
| Swivel interference | 124 mm |
| Dome diameter | 20 mm |
| Thread diameter | 0 mm |

FITTING

| | |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length | 15 mm |