

FORMA

694GUF150R26-28 S45 4XM8 GREY

EAN 4031582476286



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Forma
Type	Swivel castor with central locking (directional lock, free, wheel lock)
Load capacity at 3 km/h	135 kg
Temperature range (Minimum)	-18 °C
Temperature range (Maximum)	120 °C
Overall height	177 mm

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	18 mm
Hardness of tread (A)	60 Shore A

HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	57 mm
Swivel radius	137 mm

FITTING

Fitting type	Stem with cam hole for profile bars
Bolt diameter	28 mm
Bolt length	97 mm

FORMA

694GUF150R26-28 S45 4XM8 GREY

EAN 4031582476286



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

