

NOVATECH

FTP 125X40-Ø20 HL50

EAN 4031582331745
Order number 00841087



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	50 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204ZV
Suitable for	bt

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	480 kg
Load capacity at 6 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.51 kg

NOVATECH

FTP 125X40-Ø20 HL50

EAN 4031582331745
Order number 00841087



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

