

# EXPANDER

R07-Ø24-27 Inox\_TBE

EAN 4031582437836



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.94 in
Expander fitting (Maximum)	1.06 in
Hint	Please indicate required tube innerdiameter when ordering.

## PERFORMANCE

Corrosion resistance	● ● ● ○ ○
----------------------	-----------

## CORE ATTRIBUTES

Product name	Expander
Type	Accessory
Electric conductive	no
Stainless	Yes
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.28 lb