

MAXTECH

PNR260X75-Ø25 HL74 TFR

EAN 4031582400335



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	2.95 in
Axle hole diameter	0.98 in
Hub length	2.91 in

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Overall weight	4.3 lb

MAXTECH

PNR260X75-Ø25 HL74 TFR

EAN 4031582400335



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

