

# ALPHA STAINLESS

8470UAO160P63 BURDEOS

EAN 4031582441819



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall weight	0.927 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Hardness of tread (D)	40 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	105 mm
Plate width	80 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ALPHA STAINLESS

8470UAO160P63 BURDEOS

EAN 4031582441819



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

B470U00125P62-neu

