

DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech silent
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	250 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-30 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.3 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj, naglavljen
Boja Tocak	Prirodno belo
Prečnik	100 mm
Širina omotac	36 mm
dimenzija rupa osovina	8.4 mm
duzina glavcine	45 mm
Širina tela	36 mm
Teškoća gazećeg omotac (D)	75 Šor D

DURATECH SILENT

UOT 100x36-Ø8,4 HL45

EAN 4031582338041

Broj porudžbine 00033627
Product Drawings



BETTER MOBILITY. BETTER LIFE.

