

MAXTECH

PNP 200x30-Ø8 HL60

EAN 4031582320633



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.88 lb

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.18 in
Axle hole diameter	0.31 in
Hub length	2.36 in
Body width	1.18 in
Hardness of tread (A)	70 Shore A

MAXTECH

PNP 200x30-Ø8 HL60

EAN 4031582320633

Order number 00005569
Product Drawings



BETTER MOBILITY. BETTER LIFE.

