

PRODUCT INFORMATION

MAXTECH

UAC200x40-Ø12,5

EAN 4031582457667



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	700 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.83 kg

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	200 mm
Tread width	40 mm
Axle Hole Diameter	12.5 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	40 Shore D

MAXTECH

UAC200x40-Ø12,5

EAN 4031582457667



BETTER MOBILITY. BETTER LIFE.

Product Drawings

