PRODUCT INFORMATION

STORA

2370PIP100S74

EAN 4031582369359

BETTER MOBILITY. BETTER LIFE.

Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Stora
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.04 in

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Offset	1.38 in
Swivel radius	3.35 in
Swivel interference	6.69 in

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	75 Shore A

FITTING

Fitting type	Threaded stem with hexagon neck, top, riveted

© Copyright 2026 TENTE International GmbH