PRODUCT INFORMATION

AGILA

2477PIO100R07-Ø21,5-24

EAN 4031582372182



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	132.28 lb
Electric conductive	no
Stainless	no
Load capacity Static	264.55 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.43 in

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	1.71 in
Swivel radius	5.16 in
Swivel interference	10.31 in

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.85 in
Expander fitting (Maximum)	0.94 in
Hint	Please indicate required tube innerdiameter when ordering.

© Copyright 2026 TENTE International GmbH


AGILA

2477PIO100R07-Ø21,5-24

EAN 4031582372182

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH