

# NOVATECH

ETP 075X62-Ø20 HL62

EAN 4031582318494  
Order number 00806197



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	75 mm
Tread width	62 mm
Axle hole diameter	20 mm
Hub length	62 mm
Body width	62 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	550 kg
Load capacity at 6 km/h	440 kg
Load capacity Static	1100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.827 kg

# NOVATECH

ETP 075X62-Ø20 HL62

EAN 4031582318494  
Order number 00806197



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

